Rittal – The System.

Faster – better – everywhere.




# SV 9677.951

# Current Transformers

State: 11/15/2026 (Source: www.rittal.com/us-en)

# SV 9677.951 - Current Transformers

For inductive measurement of current flow.

## Features

| | |
|---|---|
| Model No. | SV 9677.951 |
| Product description | Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly. |
| Material | Polyamide |
| For size | 2/3 |
| Suitable for Model No. | 9677.260<br>9677.265<br>9677.280<br>9677.360<br>9677.365<br>9677.380<br>9677.930 |
| Rated output | 1.5 VA |
| Type of connection (electrical) | Box terminal |
| Insuslation material (class) | H |
| Primary current | 400 A |
| Accuracy Class | 1 |
| Test specification | IEC 60 044-1<br>EN 60715<br>DIN VDE 0414<br>DIN 42 600-2 |
| Connection of round conductors | 2.5 - 4 mm² |
| Rated frequency | 50 - 60 Hz |
| Packaging unit | 1 pc(s). |
| Net weight | 0.136 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Gross weight | 0.146 kg |
| Customs tariff number | 85043129 |
| ETIM 9 | EC002048 |
| ECLASS 8.0 | 27141146 |
| Product description | SV Current transformer 400 A/5 A for NH switch disconnectors size 2-3 / Adapter for RiLine Compact (SV 9677.XXX) |