#### Rittal - The System.

Faster – better – everywhere.





# VX 9680.005 Baying-enclosure system VX25

State: 12/14/2025 (Source: rittal.com/us-en)



## VX 9680.005 - Baying-enclosure system VX25 Isolator enclosure

Baying system for the distribution of electrical power with slimline fuse-switch disconnectors (from ABB or Jean Müller).







#### **Features**

Model No.	VX 9680.005
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame
	Door
	Roof plate
	Rear panel
	Base Plates
	Front Trim Panels
	Lock: 3 mm double-bit
	Compartment side panels
	Locating frame for isolators with fuses (brands ABB SlimLine/Jean
	Müller SASIL)

© Rittal 2025

#### Features

Protection category IP to EN 60 529	Up to IP 2X (depending on the panels)
Test specification	IEC 61 439-1/-2
	IEC 61 641
Dimensions	Width: 1,000 mm
	Height: 2,000 mm
	Depth: 600 mm
	Width: 39.4 "
	Height: 78.7 "
	Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	125.3
Gross weight	136.2
PCF/VE (cradle-to-gate)	308.7 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
EAN	4028177937062
ETIM 9	EC000261
ECLASS 8.0	27180101

### Approvals

Certificates	Surface finish
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3