

Rittal – The System.

Faster – better – everywhere.



VX 9680.227

Baying-enclosure system VX25

State: 6/30/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9680.227 - Baying-enclosure system VX25 Isolator enclosure

Baying system for the distribution of electrical power with slimline fuse-switch disconnectors (from ABB or Jean Müller).

Features

Model No.	VX 9680.227
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Door Roof plate Rear panel Base Plates Front Trim Panels Lock: 3 mm double-bit Compartment side panels Locating frame for isolators with fuses (brands ABB SlimLine/Jean Müller SASIL)
Protection category IP to EN 60 529	Up to IP 3X, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 1,200 mm Height: 2,200 mm Depth: 800 mm Width: 47.2 " Height: 86.6 " Depth: 31.5 "

Features

Packaging unit	1 pc(s).
Net weight	158.95
Gross weight	176.4
PCF per pack (cradle-to-gate)	391.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177937055
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK