
Rittal – The System.

Faster – better – everywhere.



VX 9680.608

Modular enclosure

State: 11/4/2026 (Source: www.rittal.com/us-en)

VX 9680.608 - Modular enclosure Baying-enclosure system VX25

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

Features

Model No.	VX 9680.608
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Rear panel Base Plates
Protection category IP to EN 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 ″ Height: 78.7 ″ Depth: 31.5 ″
Packaging unit	1 pc(s).
Net weight	44.7 kg
Gross weight	49.2 kg
PCF/VE (cradle-to-gate)	132.3 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	VX Modular enclosure, WHdepth 600x2000x800 mm, sheet steel

Approvals

Certificates	Surface finish