
Rittal – The System.

Faster – better – everywhere.



# VX 9680.806

# Modular enclosure

State: 11/4/2026 (Source: www.rittal.com/us-en)

# VX 9680.806 - Modular enclosure Baying-enclosure system VX25

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

## Features

| | |
|---|---|
| Model No. | VX 9680.806 |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed<br>Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Base plates: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Enclosure frame<br>Rear panel<br>Base Plates |
| Protection category IP to EN 60 529 | Up to IP 54, depending on the panels |
| Test specification | IEC 61 439-1/-2<br>IEC 61 641 |
| Dimensions | Width: 800 mm<br>Height: 2,000 mm<br>Depth: 600 mm<br>Width: 31.5 ″<br>Height: 78.7 ″<br>Depth: 23.6 ″ |
| Packaging unit | 1 pc(s). |
| Net weight | 49.3 kg |
| Gross weight | 53.8 kg |
| PCF/VE (cradle-to-gate) | 150.3 kg CO2 eq (Cat B) |

# Features

| | |
|---|---|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | VX Modular enclosure, WHdepth 800x2000x600 mm, sheet steel |

# Approvals

| | |
|---|---|
| Certificates | Surface finish |