


# Rittal – The System.

Faster – better – everywhere.



## SV 9681.204

## Perforated mounting strip

State: 9/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9681.204 - Perforated mounting strip for partial door

For retro-fitting to partial doors, with 25 mm hole pattern for individual mountings on the rear of the door, e.g. cable ducts, conduit holders etc.



## Features

Model No.	SV 9681.204
Product description	For retrofitting to partial doors. The perforated mounting strips have a 25 mm hole pattern and can be used for individual attachments such as cable ducts, hose holders, etc., and are used on the back of the doors. Hole diameter of the perforated mounting strip: 4.5 mm.
Material	Carbon steel, 1 mm
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	198 mm 7.8 "
Mounting tip	For enclosure width 1000 mm: 1 x 9681.204 and 1 x 9681.206
Dimensions	Length: 198 mm Length: 7.8 "
Suitable for	Width: 400 mm Width: 15.7 "
OUT_SUITABLE_FOR_PARTIAL_DO OR_HEIGHTS	200 - 800 mm 7.87 - 31.5 "
Packaging unit	10 pc(s).
Net weight	0.6

# Features

PCF/VE (cradle-to-gate)	2.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177930353
ETIM 9	EC000386
ECLASS 8.0	27400501

# Approvals

Explanations	Declaration of conformity UK
--------------	------------------------------