

Rittal – The System.

Faster – better – everywhere.



PK 9521.100

PK Polycarbonate Housings

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9521.100 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

| | |
|------------------------------------|--|
| Model No. | PK 9521.100 |
| Version | PK housing with transparent cover |
| Product description | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment. |
| Material | Housing: Fiber-glass reinforced polycarbonate Cover transparent: Polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polythene |
| Color | RAL 7035 |
| Supply includes | Housing with cover Cover screws Insulating bungs for wall mounting screws |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60529 | IP 66 |
| IK code | IK08 |

Features

| | |
|-----------------------------|---|
| Dimensions | Width: 254 mm Height: 180 mm Depth: 111 mm Width: 10 " Height: 7.09 " Depth: 4.37 " |
| Operating temperature range | -35 °C...80 °C -31 °F...176 °F |
| Base material | Polycarbonate |
| Packaging unit | 1 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 0.9 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | PK Polycarbonate enclosure, WHD: 254x180x111 mm, fibreglass-reinforced polycarbonate, without knockouts, with transparent cover |

Approvals

| | |
|--------------|---------------------------|
| Approvals | C-UL DNV UL |
| Explanations | Declaration of conformity |
