

Rittal – The System.

Faster – better – everywhere.



SV 9635.110

Circuit-Breaker Component Adaptors

State: 8/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.110 - Circuit-Breaker Component Adaptors 3-pole

For mechanical attachment and the direct contact of circuit breakers on the board.

Features

Model No.	SV 9635.110
Function principle	For mechanical attachment and direct contact of circuit breakers on the board Mounting the circuit breaker with variably adjustable fastening points (M4)
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Note	When selecting the CB device adapter, pay attention to the mounting distance of the circuit breaker There may be a reduction in power depending on the circuit breaker used The technical data may vary for UL applications.
Rated current max.	160 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Dimensions	Width: 90 mm Height: 160 mm Depth: 45 mm Width: 3.54 " Height: 6.3 " Depth: 1.77 "
Distance between fixing points	30 mm
Cable outlet	Top/bottom
To fit manufacturer (model)	ABB (XT2) Allen Bradley (140G-H) Eaton (NZM1)

Features

Packaging unit	1 pc(s).
Net weight	0.55
Gross weight	0.588
Copper weight (kg per piece)	0.276
Customs tariff number	85369095
EAN	4028177951846
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK