Rittal – The System.

Faster – better – everywhere.





SV 9635.210 Connection Adapters

State: 12/1/2025 (Source: rittal.com/us-en)



SV 9635.210 - Connection Adapters RiLine Compact

For connecting round conductors.

Features

Model No.	SV 9635.210
Function principle	To supply power to the board
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 7035
Note	The technical data may vary for UL applications.
Note on Model No.:	Can be used as center feed or as longitudinal connector of two bayed boards
Rated current max.	125 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Cable outlet	Top/bottom
Electrical UL ratings	Rated operating voltage (max.) UL: 600 V AC480 V AC
Type of connection (electrical)	Box terminal
Connection of round conductors, fine wire without wire end ferrule	6 - 50 mm²
Connection of round conductors, fine wire with wire end ferrule	6 - 50 mm²
Connection of round conductors, multi-wire	6 - 50 mm²
Connection of round conductors, single-wire	6 - 50 mm²
Connection for round conductor	AWG 1 - 10

© Rittal 2025

Features

Dimensions	Width: 45 mm
	Height: 160 mm
	Depth: 92.5 mm
	Width: 1.77 "
	Height: 6.3 "
	Depth: 3.64 "
Packaging unit	4 pc(s).
Net weight	1.12
Gross weight	1.183
Copper weight (kg per piece)	0.04
Customs tariff number	85369010
EAN	4028177934603
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3