

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.021 Energy-saving enclosure

State: 5/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9690.021 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular expansion of energy storage with component shelves.

## Features

Model No.	SV 9690.021
Version	Without interior fitting
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60529	IP 20
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	51 kg
Gross weight	51.9 kg
PCF/VE (cradle-to-gate)	169.87 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

# Features

---

Customs tariff number	94032080
ETIM 9	EC000261
Product description	VX ESS energy storage enclosure, WHD: 600x2,000x800 mm, with door, rear panel

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------