

Rittal – The System.

Faster – better – everywhere.



SV 9690.023

Energy storage enclosure

State: 6/29/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.023 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular energy storage installation with component shelves.

Features

Model No.	SV 9690.023
Version	Without interior fit-out
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60529	IP 20
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	67
Gross weight	67.7
PCF per pack (cradle-to-gate)	221.54 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

EAN	4028177043893
-----	---------------

ETIM 9	EC000261
--------	----------

Approvals

Explanations	Declaration of conformity
--------------	---------------------------