

Rittal – The System.

Faster – better – everywhere.



SV 9690.033 Energy storage frame

State: 5/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.033 - Energy storage frame VX ESS

Enclosure frame with flexible interior fitting. Ideal for efficient and modular expansion of energy storage.

Features

| | |
|-------------------------------------|---|
| Model No. | SV 9690.033 |
| Material | Enclosure frame: Carbon steel, 1.5 mm Profile rails: carbon steel, 2 mm Crossbar with mounting bracket: sheet steel, 3 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Profile rails: Zinc-plated Crossbar with mounting bracket: galvanized |
| Color | RAL 7035 |
| Supply includes | Enclosure frame |
| Dimensions | Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 " |
| Packaging unit | 1 pc(s). |
| Net weight | 54 kg |
| Gross weight | 54.8 kg |
| PCF/VE (cradle-to-gate) | 137.31 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| Product description | VX ESS energy storage frame, WHD: 800x2,000x800 mm, with interior fitting |