

Rittal – The System.

Faster – better – everywhere.



SV 9665.760 Cable entry flange

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9665.760 - Cable entry flange for roof plate

Cable entry gland for roof plates, with metric knockouts, seal membranes, cable entry glands, or solid.



Features

Model No.	SV 9665.760
Version	2 x M25/32/40, 1 x M32/40/50, 2 x M40/50/63
Product description	For simple, secure cable entry in the roof zone.
Material	Insulating material
Color	RAL 7035
Supply includes	Seal
No. of metric knockouts	2 x M25/M32/M40 1 x M32/M40/M50 2 x M40/M50/M63
Dimensions	Width: 250 mm Depth: 160 mm Width: 9.84 " Depth: 6.3 "
Protection category IP to IEC 60529	IP 55
Packaging unit	1 pc(s).
Net weight	0.25 kg
Gross weight	0.281 kg
Customs tariff number	39269097

Features

ETIM 9	EC000211
ECLASS 8.0	27142421
Product description	SV Cable entry gland, 2xM25/32/40, 1xM32/40/50, 2xM40/50/63, insulating material
