



# Rittal – The System.

Faster – better – everywhere.



## SV 9690.043

## Energy-saving enclosure

State: 1/22/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))



FRIEDHELM LOH GROUP

# SV 9690.043 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fitting. Ideal for efficient and modular expansion of energy storage with slide rails.

## Features

Model No.	SV 9690.043
Version	With flexible interior fitting
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60 529	IP 20
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 "
PCF/VE (cradle-to-gate)	290.48 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177044319
ETIM 9	EC000261

# Approvals

---

Explanations

Declaration of conformity