


Rittal – The System.

Faster – better – everywhere.



SV 9666.350

Connection terminal block

State: 4/6/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.350 - Connection terminal block

To connect copper and aluminum conductors and laminated copper bars.

Features

Model No.	SV 9666.350
Product description	For connecting copper and aluminum conductors. For laminated copper bars or solid and stranded conductors with crimped ferrules.
Material	Duroplastic
Color	RAL 7035
Supply includes	Assembly components
Mounting tip	Contact hazard protection module 9666.020 is required to cover the connection terminal block
Rated current max.	400 A
Number of poles	5-pole
Connection of round conductors	50 - 240 2 x 25 - 120
Clamping area for laminated copper bars (W x H)	25 x 21 mm 0.98 x 0.83 "
Packaging unit	1 pc(s).
Net weight	4.807 kg
Gross weight	5.08 kg
Customs tariff number	39211900
ETIM 9	EC001894
ECLASS 8.0	27400613
Product description	SV Connection terminal block (ISV), 400 A, 690 V, 5-pole, round conductor connection, 1x50-240/2x25-120 mm ² , clamping area BH: 25x21 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK