Rittal – The System.

Faster – better – everywhere.



SV 9676.700
Connection Plate

State: 11/5/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9676.700 - Connection Plate For cable lugs

For connection of ring terminals/lugs to a Flat-PLS busbar system with 2 – 4 bars per conductor.

Features

Model No.	SV 9676.700
Product description	For connecting cable lugs to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu, nickel-plated Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws) Threaded pin
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply Busbar claw with threaded insert M10
Rails per conductor	2
Dimensions	Thread: M12
Mounting dimensions	20 mm 0.79 ″
Packaging unit	1 pc(s).
Net weight	0.6 kg
Gross weight	0.612 kg
Copper weight (kg per piece)	0.49
Customs tariff number	73269098
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection plate, with bolts M12, (Flat-PLS)

© Rittal 2026

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK