Rittal – The System.

Faster – better – everywhere.



SV 9676.747
Connection Plate

State: 10/31/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9676.747 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

Features

Model No.	SV 9676.747
Product description	For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply Busbar claw with threaded insert M10
Rails per conductor	2
Mounting dimensions	50 mm 1.97 ″
Clamping area for laminated copper bars (W x H)	32 x 20 mm 1.26 x 0.79 ″
Suitable for laminated copper bars	Qty.: 2 Number of lamina: 10 Lamina width: 32 mm Lamina thickness: 1 mm Lamina width: 1.26 ″ Lamina thickness: 0.04 ″
Packaging unit	1 pc(s).
Net weight	0.34 kg
Gross weight	0.346 kg
Copper weight (kg per piece)	0.13

Features

Customs tariff number	73269098
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection plate, clamping area WH: 32x20 mm, (Flat-PLS)

Approvals

Explanations	Declaration of conformity Declaration of conformity UK