

# Rittal – The System.

Faster – better – everywhere.



CS 9774.510

CS Toptec

State: 2/14/2026 (Source: [rittal.com/us-en](https://rittal.com/us-en))



# CS 9774.510 - CS Toptec

Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.



## Features

Model No.	CS 9774.510
Version	Without cut-out
Product description	Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.
Material	Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035

# Features

Supply includes	Double-walled outdoor housing, fully preconfigured Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027 Side panels left and right Rear panel Rain canopy Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear
Dimensions	Width: 600 mm Height: 1,800 mm Depth: 600 mm Width: 23.6 " Height: 70.9 " Depth: 23.6 "
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
IK code	IK10
Note	All enclosure panels are double wall and grounded (external wall to internal wall) CS Toptec is the foundation for project solutions in the outdoor sector. It can be requested under these order numbers: For individual installations: 9774.099, for baying: 9774.005
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	86
Gross weight	88
Customs tariff number	94032080
EAN	4028177963139
ETIM 9	EC000261
ECLASS 8.0	27180101

# Approvals

---

Explanations

Declaration of conformity