

# Rittal – The System.

Faster – better – everywhere.



## CS 9781.666 CS Toptec, bayable

State: 6/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9781.666 - CS Toptec, bayable

Bayable, double-walled outdoor housing with 100 mm base, door, rear panel, and seamlessly bayable weatherproof roof. The complete enclosure frame is available for efficient and flexible interior fitting.



## Features

|                 |  |
|-----------------|--|
| Model No.       | CS 9781.666  |
| Version         | For baying<br>Without cut-out  |
| Material        | Housing frame: Stainless steel 1.4301 (AISI 304)<br>Enclosure panels and base/plinth panels: Aluminum, AlMg3<br>Rain canopy: Aluminum  |
| Surface finish  | Powder-coated<br>UV-resistant pure polyester   |
| Color           | RAL 7035   |
| Supply includes | Bayable, double-walled outdoor housing<br>Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels<br>Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027<br>Rear panel<br>Rain canopy<br>Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear<br>Door hinged on the right, may be swapped to the left |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 600 mm<br>Height: 1,600 mm<br>Depth: 600 mm<br>Width: 23.6 "<br>Height: 63 "<br>Depth: 23.6 "  |
| Dimensions                          | Overall height: 1,745 mm<br>Rain canopy height: 45 mm<br>Height of base/plinth: 100 mm<br>Rain canopy height: 1.77 "<br>Height of base/plinth: 3.94 "                   |
| Number of doors                     | 1   |
| Lock                                | Lock version: 4-point locking system<br>No. of locks: 1<br>Lock Insert: BJ20027   |
| Gland plate                         | Size: 2<br>Qty.: 2  |
| Protection category IP to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 3R<br>NEMA 12  |
| IK code                             | IK10  |
| Note                                | All enclosure panels are double wall and grounded (external wall to internal wall)<br>For the assembly of an enclosure, side panels for CS Toptec, bayable are required |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 55 kg   |
| Gross weight                        | 65 kg   |
| Customs tariff number               | 94032080  |
| ETIM 9                              | EC000261  |
| ETIM 8                              | EC000261  |
| ECLASS 8.0                          | 27180101  |

# Features

---

Product description

CS Toptec, bayable, WHD: 600x1600x600 mm

# Approvals

---

Explanations

Declaration of conformity