

**Rittal – The System.**

Faster – better – everywhere.



# SV 9676.749 Connection Plate

State: 5/14/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9676.749 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

## Features

Model No.	SV 9676.749
Product description	For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply Busbar claw with threaded insert M10
Rails per conductor	2
Mounting dimensions	50 mm 1.97 "
Clamping area for laminated copper bars (W x H)	100 x 20 mm 3.94 x 0.79 "
Suitable for laminated copper bars	Qty.: 2 Number of lamina: 10 Lamina width: 100 mm Lamina thickness: 1 mm Lamina width: 3.94 " Lamina thickness: 0.04 "
Packaging unit	1 pc(s).
Net weight	0.62 kg
Gross weight	0.639 kg
Copper weight (kg per piece)	0.27

# Features

---

Customs tariff number	73269098
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection plate, clamping area WH: 100x20 mm, (Flat-PLS)

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---