Rittal - The System.

Faster – better – everywhere.





SV 9677.110 NH In-line Fuse-Switch Disconnector

State: 12/14/2025 (Source: rittal.com/us-en)



SV 9677.110 - NH In-line Fuse-Switch Disconnector

3-pole, for busbar systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.110
Version	1-pole, switchable
Material	Polyamide
	Fire protection corresponding to UL 94-V0
	Contact tracks: Partially silver-plated hard copper
Color	Chassis: RAL 7035
	Cover: RAL 7001
	Handle: RAL 7016
For NH size	1
For bar systems with center-to- center spacing	185 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Bolt M12
Number of poles	3-pole
Rated operating voltage	800 V (AC), 3~
Rated operating current max.	250 A
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Test specification	IEC 60 947-3
	IEC 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 100 mm
	Height: 670 mm
	Width: 3.94 "
	Height: 26.4 "
Connection of round conductors	6 - 240 mm²

© Rittal 2025

Features

Suitable for busbars	Height: 10 mm Height: 0.39 "
Packaging unit	1 pc(s).
Net weight	4.9
Gross weight	4.94
Copper weight (kg per piece)	1.73
Customs tariff number	85365080
EAN	4028177705494
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3