Rittal – The System.

Faster – better – everywhere.



SV 9677.340

NH In-line Fuse-Switch Disconnector

State: 11/14/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9677.340 - NH In-line Fuse-Switch Disconnector

3-pole, for busbar systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.340
Version	3-pole, switchable
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Partially silver-plated hard copper
Color	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For NH size	3
For bar systems with center-to-center spacing	185 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Bolt M12
Number of poles	3-pole
Rated operating voltage	690 V (AC), 3~
Rated operating current max.	1,250 A
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 200 mm Height: 670 mm Width: 7.87 ″ Height: 26.4 ″
Connection of round conductors	6 - 240 mm²

© Rittal 2026

Features

Suitable for busbars	Height: 10 mm Height: 0.39 ″
Double disconnector	Yes
Packaging unit	1 pc(s).
Net weight	14 kg
Gross weight	14.4 kg
Copper weight (kg per piece)	6.838
Customs tariff number	85365080
ETIM 9	EC001046
ECLASS 8.0	27371402
Product description	SV NH slimline fuse-switch disconnector, size 3, 1250 A, 690 V, 3-pole, twin track, bolt M12, 185 mm, for current transformer installation

Approvals

Explanations	Declaration of conformity Declaration of conformity UK