Rittal – The System.

Faster – better – everywhere.



SV 9677.700
Component Adapters

State: 11/3/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9677.700 - Component Adapters Terminal fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.700
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
For bar systems with center-to-center spacing	185 mm
Cable outlet	Bottom
Installation type	Clamping attachment
Number of poles	3-pole
Rated current max.	1,000 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For mounting on busbar systems with or without cover section
Dimensions	Width: 300 mm Height: 652 mm Width: 11.8 ″ Height: 25.7 ″
Suitable for busbars	Height: 10 mm Height: 0.39 ″
To fit manufacturer (model)	ABB (XT6, XT7 – 800 A/1000 A) Eaton (NZM4 - 800 A/1000 A) Schneider Electric (NS - 800 A/1000 A) Siemens (3VA27 - 800 A/1000 A)
Packaging unit	1 pc(s).
Net weight	13.3 kg

© Rittal 2026

Features

Gross weight	15.28 kg
Copper weight (kg per piece)	7.745
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor, 1000 A, 690 V, 3-pole, 185 mm, clamping attachment

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK