

Rittal – The System.

Faster – better – everywhere.



CS 9828.500

CS Toptec

State: 8/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9828.500 - CS Toptec

Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.



Features

Model No.	CS 9828.500
Version	Without cut-out
Product description	Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.
Material	Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035

Features

Supply includes	<p>Double-walled outdoor housing, fully preconfigured</p> <p>Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels</p> <p>Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027</p> <p>Side panels left and right</p> <p>Rear panel</p> <p>Rain canopy</p> <p>Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 1,200 mm</p> <p>Depth: 800 mm</p> <p>Width: 31.5 "</p> <p>Height: 47.2 "</p> <p>Depth: 31.5 "</p>
Protection category IP to IEC 60529	IP 55
IK code	IK10
Note	<p>All enclosure panels are double wall and grounded (external wall to internal wall)</p> <p>CS Toptec is the foundation for project solutions in the outdoor sector. It can be requested under these order numbers: For individual installations: 9774.099, for buying: 9774.005</p>
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	96
Gross weight	98
EAN	4028177962743
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Explanations

Declaration of conformity