

**Rittal – The System.**

Faster – better – everywhere.



# SV 9677.780 Component Adapters

State: 7/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.780 - Component Adapters Screw fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

## Features

Model No.	SV 9677.780
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Connection straps
For bar systems with center-to-center spacing	185 mm
Cable outlet	Bottom
Installation type	Screw attachment
Number of poles	3-pole
Rated current max.	630 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal for fastening to perforated busbars. Note that no cover sections are fitted in the vicinity of the device.
Dimensions	Width: 150 mm Height: 585 mm Width: 5.91 " Height: 23 "
Suitable for busbars	Height: 10 mm Height: 0.39 "
To fit manufacturer (model)	ABB (Tmax T5) Eaton (NZM3) Schneider Electric (NSX630) Siemens (3VA23, 3VA24, 3VL4)

# Features

---

Packaging unit	1 pc(s).
Net weight	5.92 kg
Gross weight	6.32 kg
Copper weight (kg per piece)	3.652
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor, 630 A, 690 V, 3-pole, 185 mm, screw attachment

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK