

Rittal – The System.

Faster – better – everywhere.



SV 9677.810 Current Transformers

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.810 - Current Transformers

For inductive measurement of current flow.

Features

| | |
|---------------------------------|--|
| Model No. | SV 9677.810 |
| Product description | Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly. |
| Material | Polyamide |
| For size | 00 |
| Suitable for Model No. | 9677000 9677010 9677015 9677025 9677060 9677065 9677070 9677075 9677080 9677085 |
| Rated output | 2.5 VA |
| Type of connection (electrical) | Screw clamps |
| Insulation material (class) | E |
| Primary current | 150 A |
| Accuracy Class | 1 |
| Test specification | IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2 |
| Connection of round conductors | 2.5 - 4 mm ² |
| Rated frequency | 50 - 50 - Hz |

Features

| | |
|-----------------------|---|
| Packaging unit | 1 pc(s). |
| Net weight | 0.2 kg |
| Gross weight | 0.21 kg |
| Customs tariff number | 85043129 |
| ETIM 9 | EC002048 |
| ECLASS 8.0 | 27141146 |
| Product description | SV current transformer, for NH slimline fuse-switch-disconnectors/ NH slimline switch-disconnectors, size 00 (SV 9677XXX), 150 A/5A, 50-60 Hz |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|