Rittal – The System.

Faster – better – everywhere.



SV 9677.865
Current Transformers

State: 11/12/2026 (Source: www.rittal.com/us-en)

SV 9677.865 - Current Transformers

For inductive measurement of current flow.

Features

Model No.	SV 9677.865
Product description	Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly.
Material	Polyamide
For size	1 - 3
Suitable for Model No.	9677.100 9677.110 9677.115 9677.200 9677.210 9677.215 9677.300 9677.310 9677.315 9677.340 9677.770 9677.780 9677.900
Rated output	2.5 VA
Type of connection (electrical)	Box terminal
Insuslation material (class)	H
Primary current	250 A
Secondary current	5 A
Accuracy Class	1

© Rittal 2026

Features

Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm²
Rated frequency	50 - 60 Hz
Packaging unit	1 pc(s).
Net weight	0.13 kg
Gross weight	0.16 kg
Customs tariff number	85044087
ETIM 9	EC002048
ECLASS 8.0	27141146
Product description	SV Current transformer 250 A/ 5 A for NH slimline fuse-switch disconnectors size 1-3 (SV 9677.XXX)

© Rittal 2026