
Rittal – The System.

Faster – better – everywhere.



SV 9677.910
Connection block

State: 11/14/2026 (Source: www.rittal.com/us-en)

SV 9677.910 - Connection block

For connecting cables and laminated copper bars.

Features

Model No.	SV 9677.910
Product description	For connecting conductors or laminated copper bars.
Material	Carbon steel, zinc-plated E-Cu, tin-plated
Clamping area height	20 mm 0.79 ″
Clamping area width	80 mm 3.15 ″
Cable outlet	Top/bottom
Rated current max.	1,600 A
Dimensions	Width: 98 mm Width: 3.86 ″
Suitable for busbars	Height: 10 mm Height: 0.39 ″
Packaging unit	1 pc(s).
Net weight	0.9 kg
Gross weight	0.982 kg
Copper weight (kg per piece)	0.689
PCF/VE (cradle-to-gate)	3.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613

Features

Product description	SV Connection block, 1600 A, 690 V, 1-pole, cable outet top/bottom

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK