
## Rittal - The System.

Faster - better - everywhere.





# SV 9677.920 Connection block

State: 12/10/2025 (Source: rittal.com/us-en)



#### SV 9677.920 - Connection block

For connecting cables and laminated copper bars.

#### **Features**

Model No.	SV 9677.920
Product description	For connecting conductors or laminated copper bars.
Material	Carbon steel, zinc-plated E-Cu, tin-plated
Cable outlet	Top/bottom
Type of connection (electrical)	Ring terminal M12
Rated current max.	1,600 A
Dimensions	Width: 98 mm Width: 3.86 ″
Connection of round conductors	240 mm²
Suitable for busbars	Height: 10 mm Height: 0.39 "
Packaging unit	1 pc(s).
Net weight	1.6
Gross weight	1.662
Copper weight (kg per piece)	1.471
PCF/VE (cradle-to-gate)	6.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369095
EAN	4028177806351
ETIM 9	EC002270
ECLASS 8.0	27400613

© Rittal 2025

### Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3