



# SV 9677.950 - Current Transformers

For inductive measurement of current flow.

## Features

Model No.	SV 9677.950
Product description	Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly.
Material	Polyamide
Suitable for Model No.	9677.160 9677.165 9677.180 9677.260 9677.265 9677.280 9677.360 9677.365 9677.380 9677.930
Rated output	1.5 VA
Type of connection (electrical)	Box terminal
Insulation material (class)	H
Primary current	250 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm <sup>2</sup>
Rated frequency	50 - 60 Hz

# Features

Packaging unit	1 pc(s).
Net weight	0.13 kg
Gross weight	0.14 kg
Customs tariff number	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146
Product description	SV Current transformer 250 A/5 A for NH switch disconnectors size 1-3 / Adapter for RiLine Compact (SV 9677.XXX)