Rittal – The System.

Faster – better – everywhere.



SV 9677.958
Current Transformers

State: 11/11/2026 (Source: www.rittal.com/us-en)

SV 9677.958 - Current Transformers

For inductive measurement of current flow.

Features

Model No.	SV 9677.958
Product description	Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly.
Material	Polyamide
Suitable for Model No.	9677930
Rated output	2.5 VA
Type of connection (electrical)	Box terminal
Insuslation material (class)	H
Primary current	800 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm²
Rated frequency	50 - 60 Hz
Packaging unit	1 pc(s).
Net weight	0.16 kg
Gross weight	0.17 kg
Customs tariff number	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146

© Rittal 2026

Features

Product description	SV Current Transformer 800 A/5 A for RiLine Compact 185 mm adapter (SV 9677.930)