


Rittal – The System.

Faster – better – everywhere.



VX 9680.025

Baying-enclosure system VX25

State: 1/9/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

VX 9680.025 - Baying-enclosure system VX25 Isolator enclosure

Baying system for the distribution of electrical power with slimline fuse-switch disconnectors (from ABB or Jean Müller).



Features

Model No.	VX 9680.025
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Door Roof plate Rear panel Base Plates Front Trim Panels Lock: 3 mm double-bit Compartment side panels Locating frame for isolators with fuses (brands ABB SlimLine/Jean Müller SASIL)

Features

Protection category IP to EN 60 529	Up to IP 2X (depending on the panels)
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 1,000 mm Height: 2,200 mm Depth: 600 mm Width: 39.4 " Height: 86.6 " Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	135.2
Gross weight	146.4
PCF/VE (cradle-to-gate)	333.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177937048
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK