


Rittal – The System.

Faster – better – everywhere.



TS 9982.224 TS IT High Density

State: 7/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 9982.224 - TS IT High Density

TS IT Enclosure for use with row-based high-density LCP climate control systems.

Features

Model No.	TS 9982.224
Product description	TS IT LCP Ready, 19" mounting angles, viewing door, WHD: 800 x 2200 x 1200 mm, 47 U
Material	Carbon steel Viewing door: Polycarbonate, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005
Supply includes	Enclosure frame with front and rear door Viewing door, front, 130° hinges Carbon steel door rear, closed, one-piece, 130° hinges Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting 50 multi-tooth screws M6, captive nuts M6, conductive (supplied loose) Vertical brush baffles Roof plate, multi-piece, removable, with full depth side cable entry Base, gland plate(s)
Dimensions	Width: 800 mm Height: 2,200 mm Depth: 1,200 mm Width: 31.5 " Height: 86.6 " Depth: 47.2 "
Height units	47 U

Features

Mounting space to 19" level, front/ rear	100 mm / 363 mm
Distance between mounting levels	742 mm 29.2 "
Design doors	Closed
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Customs tariff number	9403200082
