


Rittal – The System.

Faster – better – everywhere.



VX 9680.606

Baying-enclosure system VX25

State: 4/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9680.606 - Baying-enclosure system VX25 Modular enclosure

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

Features

Model No.	VX 9680.606
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Rear panel Base Plates
Protection category IP to EN 60529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 600 mm Width: 23.6 " Height: 78.7 " Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	41.82 kg
Gross weight	45.2 kg
PCF/VE (cradle-to-gate)	125.7 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	VX Modular enclosure, WHdepth 600x2000x600 mm, sheet steel

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity UK