

# Rittal – The System.

Faster – better – everywhere.

## Cable gland HD – HD 2410.021

Date : 22.9.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Cable gland HD – HD 2410.021

created: 22.09.2020 build on [www.rittal.com/si-sl](http://www.rittal.com/si-sl)



## Product description

<b>Design:</b>	Standard
<b>Benefits:</b>	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
<b>Applications:</b>	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
<b>Material:</b>	Nut: Stainless steel 1.4305 (AISI 303) Seal: Conforms to FDA 21 CFR 177.2600
<b>Protection category IP to IEC 60 529:</b>	IP69 / IPX8 (5 bar, 30 min)
<b>Supply includes:</b>	Lock nut

## Product features

<b>Ambient temperature range:</b>	-20 °C...+100 °C
<b>Thread:</b>	M20 x 1.5
<b>Operating temperature (max.):</b>	100 °C
<b>Cable entry:</b>	For cable diameter: 6 mm - 12 mm
<b>Packs of:</b>	5 pc(s).

<b>EAN:</b>	4028177928701
<b>Customs tariff number:</b>	73181900
<b>ETIM 7.0:</b>	EC000441
<b>ETIM 6.0:</b>	EC000441
<b>eCl@ss 8.0/8.1:</b>	27149109
<b>eCl@ss 6.0/6.1:</b>	27189265
<b>Product description:</b>	HD Cable gland, stainless steel 1.4305, size: M20x1,5, for cables Ø 6-12 mm, Standard version
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL VDE