

Rittal – The System.

Faster – better – everywhere.

▶ Thread tapping option for Perforex LC 3030 – AS 4050.318

Date : Jan 22, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Thread tapping option for Perforex LC 3030 – AS 4050.318

created: 22.01.2021 build on www.rittal.com/uae-en



Product description

Design:	Movable tool magazine with 6 magazine slots Tool holder Additional drive unit
Description:	Thread tapping option for cutting threaded holes with the Perforex laser centre LC.
Benefits:	Machining of projects with tapped holes supported Fast, automatic changeover from laser function to thread-tapping function by accommodating an additional machine head
Supply includes:	Thread tapper Clamping units for M3 – M10
To fit Model No.:	4050.330

Product features

Max. machinable height:	600 mm
Material thickness (max.):	5 mm
Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177806658

Customs tariff number:	84669360
ETIM 7.0:	EC000000
ETIM 6.0:	EC000000
eCl@ss 8.0/8.1:	36600890
eCl@ss 6.0/6.1:	36600890
Product description:	AS Tapping unit LC 3015/3030, Tapping option for Perforex Lasercenter LC, - Including equipped Tool holders M3 - M10., - Tool magazine with 6 slots., - SK30 Tool holder.