

# Rittal – The System.

Faster – better – everywhere.

## Network rack TE 8000 – TE 7888.460

Date : Aug 13, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Network rack TE 8000 – TE 7888.460

created: 13.08.2020 build on [www.rittal.com/uae-en](http://www.rittal.com/uae-en)



## Product description

<b>Benefits:</b>	No frame structure Optimum accessibility Readily dismantled and therefore easily installed Interchangeable door hinge
<b>Material:</b>	Sheet steel Glazed door: Single-pane safety glass, 3 mm
<b>Surface finish:</b>	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 20
<b>Supply includes:</b>	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, including 130° hinge, designer handle and security lock 3524 E Sheet steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional population with module plates) Roof plate including concealed cut-out for cable entry and optional fan 4 levelling feet, M10 (supplied loose) 4 spacers, 20 mm (supplied loose) to raise the roof plate Side panels, lockable, including security lock 3524 E
<b>Basic material:</b>	Sheet steel

## Product features

<b>Design:</b>	with side panels
<b>Dimensions:</b>	Width: 800 mm

Height: 1200 mm  
Depth: 800 mm

<b>Installation height for components:</b>	24 U
<b>Distance between levels as delivered:</b>	495 mm
<b>Free mounting space to the 482.6 mm (19") level, front/rear:</b>	130 mm / 130 mm
<b>Load capacity:</b>	4000 N
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	74 kg
<b>EAN:</b>	4028177801448
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC002499
<b>ETIM 6.0:</b>	EC002499
<b>eCl@ss 8.0/8.1:</b>	27180207
<b>eCl@ss 6.0/6.1:</b>	27180207
<b>Product description:</b>	TE Network enclosure TE 8000, WHD: 800x1200x800 mm, 24 U, With glazed door
<b>Approvals</b>	
<b>Declarations:</b>	Declaration of conformity