


Rittal – The System.

Faster – better – everywhere.



SV 9683.563

Partial Mounting Panel

State: 2/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9683.563 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

Features

Model No.	SV 9683.563
Version	with insulating material gland
Product description	For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible.
Material	Carbon steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly components
For compartment height	300 mm 11.8 "
Dimensions	Width: 502 mm Height: 293 mm Width: 19.8 " Height: 11.5 "
Suitable for	Width: = 600 mm Width: = 23.6 "
Packaging unit	1 pc(s).
Net weight	3.32
Gross weight	3.52
PCF/VE (cradle-to-gate)	13.4 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910

Features

EAN 4028177935235

ETIM 9 EC000213

ECLASS 8.0 27400613

Approvals

Explanations Declaration of conformity UK