

Rittal – The System.

Faster – better – everywhere.



SV 9690.021 Energy-saving enclosure

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.021 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular expansion of energy storage with component shelves.

Features

| | |
|-------------------------------------|--|
| Model No. | SV 9690.021 |
| Version | Without interior fitting |
| Material | Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint |
| Color | RAL 7035 |
| Supply includes | Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit |
| Protection category IP to EN 60529 | IP 20 |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 " |
| Packaging unit | 1 pc(s). |
| Net weight | 51 kg |
| Gross weight | 51.9 kg |
| PCF/VE (cradle-to-gate) | 169.87 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |

Features

| | |
|-----------------------|---|
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| Product description | VX ESS energy storage enclosure, WHD: 600x2,000x800 mm, with door, rear panel |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|