

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.023

### Energy-saving enclosure

State: 1/17/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))



FRIEDHELM LOH GROUP

# SV 9690.023 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular expansion of energy storage with component shelves.

## Features

Model No.	SV 9690.023
Version	Without interior fitting
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60 529	IP 20
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	67
Gross weight	67.7
PCF/VE (cradle-to-gate)	221.54 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

# Features

---

EAN 4028177043893

---

ETIM 9 EC000261

# Approvals

---

Explanations Declaration of conformity