
Rittal – The System.

Faster – better – everywhere.





SV 9690.023 Energy-saving enclosure

State: 11/19/2025 (Source: rittal.com/us-en)



SV 9690.023 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular expansion of energy storage with component shelves.

Features

Model No.	SV 9690.023
Version	Without interior fitting
Material	Enclosure frame: Carbon steel, 1.5 mm
	Roof sheet: carbon steel, 1.5 mm
	Door: Carbon steel, 1.5 mm
	Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame
	Door and rear panel, perforated
	Roof plate
	Lock: 3 mm double-bit
Protection category IP to EN 60 529	IP 20
Dimensions	Width: 800 mm
	Height: 2,000 mm
	Depth: 800 mm
	Width: 31.5 "
	Height: 78.7 "
	Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	67
Gross weight	67.7
PCF/VE (cradle-to-gate)	221.54 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

© Rittal 2025

Features

EAN	4028177043893
ETIM 9	EC000261

Approvals

Explanations Declaration of conformity

© Rittal 2025 3