

Rittal – The System.

Faster – better – everywhere.



SV 9690.030 Energy storage frame

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.030 - Energy storage frame VX ESS

Enclosure frame with flexible interior fitting. Ideal for efficient and modular expansion of energy storage.

Features

Model No.	SV 9690.030
Material	Enclosure frame: Carbon steel, 1.5 mm Profile rails: carbon steel, 2 mm Crossbar with mounting bracket: sheet steel, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Profile rails: Zinc-plated Crossbar with mounting bracket: galvanized
Color	RAL 7035
Supply includes	Enclosure frame
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 600 mm Width: 23.6 " Height: 78.7 " Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	42 kg
Gross weight	42.5 kg
PCF/VE (cradle-to-gate)	106.89 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC000261
Product description	VX ESS energy storage frame, WHD: 600x2,000x600 mm, with interior fitting