

Rittal – The System.

Faster – better – everywhere.



SV 9690.031

Energy storage frame

State: 1/17/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

SV 9690.031 - Energy storage frame VX ESS

Enclosure frame with flexible interior fitting. Ideal for efficient and modular expansion of energy storage.

Features

Model No.	SV 9690.031
Material	Enclosure frame: Carbon steel, 1.5 mm Profile rails: carbon steel, 2 mm Crossbar with mounting bracket: sheet steel, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Profile rails: Zinc-plated Crossbar with mounting bracket: galvanized
Color	RAL 7035
Supply includes	Enclosure frame
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	44
Gross weight	44.4
PCF/VE (cradle-to-gate)	111.06 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177044197
ETIM 9	EC000261