

Rittal – The System.

Faster – better – everywhere.



SV 9690.041

Energy storage enclosure

State: 6/7/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.041 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fit-out. Ideal for efficient and modular energy storage installation with slide rails.

Features

Model No.	SV 9690.041
Version	With flexible interior fit-out
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60529	IP 20
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	68.1
Gross weight	72.1
PCF per pack (cradle-to-gate)	216.29 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

EAN	4028177044296
ETIM 9	EC000261

Approvals

Explanations	Declaration of conformity
--------------	---------------------------