


Rittal – The System.

Faster – better – everywhere.



SV 9690.041

Energy-saving enclosure

State: 8/26/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.041 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fitting. Ideal for efficient and modular expansion of energy storage with slide rails.

Features

Model No.	SV 9690.041
Version	With flexible interior fitting
Material	Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint
Color	RAL 7035
Supply includes	Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit
Protection category IP to EN 60529	IP 20
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 800 mm Width: 23.6 " Height: 78.7 " Depth: 31.5 "
Packaging unit	1 pc(s).
Net weight	68.1
Gross weight	72.1
PCF/VE (cradle-to-gate)	216.29 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

EAN	4028177044296
ETIM 9	EC000261

Approvals

Explanations	Declaration of conformity
--------------	---------------------------