

Rittal – The System.

Faster – better – everywhere.



SV 9690.043

Energy-saving enclosure

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.043 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fitting. Ideal for efficient and modular expansion of energy storage with slide rails.

Features

| | |
|-------------------------------------|--|
| Model No. | SV 9690.043 |
| Version | With flexible interior fitting |
| Material | Enclosure frame: Carbon steel, 1.5 mm Roof sheet: carbon steel, 1.5 mm Door: Carbon steel, 1.5 mm Rear wall: carbon steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: powder-coated, textured paint |
| Color | RAL 7035 |
| Supply includes | Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit |
| Protection category IP to EN 60529 | IP 20 |
| Dimensions | Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 " |
| PCF/VE (cradle-to-gate) | 290.48 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |

Features

Product description

VX ESS energy storage enclosure WHD: 800x2,000x800 mm, with door, rear panel, interior fitting

Approvals

Explanations

Declaration of conformity