

Rittal – The System.

Faster – better – everywhere.



CS 9750.918 Multifunction housing

State: 4/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9750.918 - Multifunction housing MFG 18

Modular housing system for outdoor siting, 3-door, double-walled, symmetric or asymmetric



Features

Model No.	CS 9750.918
Product description	Modular housing system for outdoor siting, 3-door, double-walled, symmetric or asymmetric
Benefits	Prepared for mounting of a heat exchanger or a Direct Air Cooling (DAC) system.
Material	Aluminum Mounting plate: Aluminum
Surface finish	Powder-coated Pure polyester
Color	RAL 7035

Features

Supply includes	Welded-in middle bar Right-hand door with single swivel lever, no insert Left door with double swivel lever, without insert on right, with blanking insert on left Center door locked from the inside 3x door stays using mechanical system (approx. 155°) Weather canopy, vented (height approx. 150 mm) Base plate, one-piece with cable glands: left, unit for energy supply companies (ESC part): 2x M20 and 1x M50, center 3x M50 and 2x M63, right: 4x M16, 4x M25 and 1x M32, incl. cover plugs for plastic gland One-piece 2x 19" standard bay, stainless steel throughout Mounting panel Divider panel between unit for energy supply companies (ESC part) and 482.6 mm (19") level 2 bay FM frame
Options	Symmetrically divided doors Asymmetrically divided doors Base for multi-function housing Heat Exchangers Direct Air Cooling (DAC) Systems Battery base Unit for energy supply companies (ESC part) Power supply
Dimensions	Width: 2,000 mm Height: 1,500 mm Depth: 500 mm Width: 78.7 " Height: 59.1 " Depth: 19.7 "
Number of doors	3
Protection category IP to IEC 60529	IP 55
Note on Model No.:	Delivery times on request.
Base material	Aluminum
Packaging unit	1 pc(s).
Customs tariff number	94032080

Features

ETIM 9	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------