Rittal – The System.

Faster – better – everywhere.



# CS 9781.818

# CS Toptec, bayable

State: 11/13/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# CS 9781.818 - CS Toptec, bayable

Bayable, double-walled outdoor housing with 100 mm base, door, rear panel, and seamlessly bayable weatherproof roof. The complete enclosure frame is available for efficient and flexible interior fitting.





## Features

| | |
|---|---|
| Model No. | CS 9781.818 |
| Version | For baying<br>Without cut-out |
| Material | Housing frame: Stainless steel 1.4301 (AISI 304)<br>Enclosure panels and base/plinth panels: Aluminum, AlMg3<br>Rain canopy: Aluminum |
| Surface finish | Powder-coated<br>UV-resistant pure polyester |
| Color | RAL 7035 |
| Supply includes | Bayable, double-walled outdoor housing<br>Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels<br>Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027<br>Rear panel<br>Rain canopy<br>Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear<br>Door hinged on the right, may be swapped to the left |

# Features

| | |
|---|---|
| Dimensions | Width: 800 mm<br>Height: 1,200 mm<br>Depth: 800 mm<br>Width: 31.5 ″<br>Height: 47.2 ″<br>Depth: 31.5 ″ |
| Dimensions | Overall height: 1,345 mm<br>Rain canopy height: 45 mm<br>Height of base/plinth: 100 mm<br>Rain canopy height: 1.77 ″<br>Height of base/plinth: 3.94 ″ |
| Number of doors | 1 |
| Lock | Lock version: 4-point locking system<br>No. of locks: 1<br>Lock Insert: BJ20027 |
| Gland plate | Size: 2<br>Qty.: 2 |
| Type rating according to 508A | Type 1<br>Type 3R<br>Type 12 |
| Protection category IP to IEC 60 529 | IP 55 |
| Protection category NEMA | NEMA 3R<br>NEMA 12 |
| IK code | IK10 |
| Note | All enclosure panels are double wall and grounded (external wall to internal wall)<br>For the assembly of an enclosure, side panels for CS Toptec, bayable are required |
| Packaging unit | 1 pc(s). |
| Net weight | 66 kg |
| Gross weight | 76 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |

# Features

| | |
|---|---|
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | CS Toptec, bayable, WHD: 800x1200x800 mm, overall height incl. 100 mm plinth and 45 mm rain canopy: 1345 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |