

Rittal – The System.

Faster – better – everywhere.



CS 9781.828 CS Toptec, bayable

State: 6/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9781.828 - CS Toptec, bayable

Bayable, double-walled outdoor housing with 100 mm base, door, rear panel, and seamlessly bayable weatherproof roof. The complete enclosure frame is available for efficient and flexible interior fitting.



Features

| | |
|-----------------|--|
| Model No. | CS 9781.828 |
| Version | For baying Without cut-out |
| Material | Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum |
| Surface finish | Powder-coated UV-resistant pure polyester |
| Color | RAL 7035 |
| Supply includes | Bayable, double-walled outdoor housing Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027 Rear panel Rain canopy Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear Door hinged on the right, may be swapped to the left |

Features

| | |
|-------------------------------------|---|
| Dimensions | Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 " Height: 78.7 " Depth: 31.5 " |
| Dimensions | Overall height: 2,145 mm Rain canopy height: 45 mm Height of base/plinth: 100 mm Rain canopy height: 1.77 " Height of base/plinth: 3.94 " |
| Number of doors | 1 |
| Lock | Lock version: 4-point locking system No. of locks: 1 Lock Insert: BJ20027 |
| Gland plate | Size: 2 Qty.: 2 |
| Protection category IP to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 3R NEMA 12 |
| IK code | IK10 |
| Note | All enclosure panels are double wall and grounded (external wall to internal wall) For the assembly of an enclosure, side panels for CS Toptec, bayable are required |
| Packaging unit | 1 pc(s). |
| Net weight | 86 kg |
| Gross weight | 96 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Features

Product description

CS Toptec, bayable, WHD: 800x2000x800 mm

Approvals

Explanations

Declaration of conformity