

Rittal – The System.

Faster – better – everywhere.



CS 9791.015

Outdoor Wall-mounted enclosure

State: 1/16/2026 (Source: ittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CS 9791.015 - Outdoor Wall-mounted enclosure

Outdoor housings for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation.



Features

Model No.	CS 9791.015
Product description	Outdoor housings for wall or pole mounting. Housing-within-a-housing concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation
Material	Enclosure and mounting plate: Aluminum AlMg3 Door inner casing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: powder-coated, UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygrostat Outer housing with designer cover and security lock 3524 E 2 C rails on the rear panel
Dimensions	Width: 370 mm Height: 522 mm Depth: 210 mm Width: 14.6 " Height: 20.6 " Depth: 8.27 "

Features

Clearances	Clearance width: 280 mm Clearance height: 380 mm Clearance depth: 145 mm Clearance width: 11 " Clearance height: 15 " Clearance depth: 5.71 "
Dimensions of mounting plate (W x H)	270 mm x 380 mm 10.6 " x 15 "
Inner housing	Width: 300 mm Height: 400 mm Depth: 170 mm Width: 11.8 " Height: 15.7 " Depth: 6.69 "
Lock	Lock version: Cam No. of locks: 1
Protection category IP to IEC 60529	IP 55
Note	Delivery times on request.
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	8.048
Gross weight	8.472
Customs tariff number	94032080
EAN	4028177193697
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK